

## Decon Large Spaces Effortlessly

### Room Fogging

The RDS 6110 uses an EPA-approved, hospital-grade disinfectant to completely fog large-sized treatment areas such as laboratories, surgical suites, gymnasiums, locker rooms and garages.

### Hand Apply

Use an optional AeroClave Portable Applicator (APA) to apply disinfectant by hand-spraying directly on high contact areas to spot treat patrol cars, ambulances, equipment and exterior spaces.

### Benefits

- Reduces your staffs exposure to dangerous pathogens
- Decontaminate and Disinfect even hard-to-reach surfaces
- Consistent and reliable delivery of disinfectant, not achievable through manual cleaning methods
- Fast turn around and hands-free technology allows you to redeploy staff to highest and best use
- Low cost of operation and ownership
- Safe for sensitive equipment

### Kills Harmful Bacteria, Viruses, and Fungi"

Proven effective against:

- Bacteria: MRSA, Staphylococcus aureus, E. coli, Salmonella, Pseudomonas, Legionella
- Viruses: HIV-1, Hepatitis B & C, SARS-CoV-2, Influenza A/Brazil (H1N1), Rotavirus, Norovirus, Poliovirus, Rhinovirus, Human Coronavirus, Ebola, Mpox, Bird Flu (H5N1)
- Fungi & Mold: Trichophyton mentagrophytes, Aspergillus niger
- Others: Listeria monocytogenes, Klebsiella pneumoniae

### Advanced User Interface

Our sophisticated touchscreen interface allows for minimal training to operate the RDS 6110. Facility and asset management tracking software is included, which will save run data and room configurations. Reports are available in csv file format by download to a portable USB drive.

### Multiple Applications

- EMS/Fire/Police vehicles
- Law enforcement offices, jails, and holding cells
- Hospital facilities & equipment
- Surgical suites, in and out-patient facilities
- Laboratories & research facilities
- \* Nursing homes
- "Assisted Living Facilities
- Veterinary hospitals and animal shelters
- Athletic facilities & sports equipment
- Schools & childcare facilities
- Cruise ships and hotels
- And More



# OPTIONAL ACCESSORIES AND CONSUMABLES



## ADP-RM

Automated, hands-free disinfection solution for enclosed spaces like offices, classrooms, and patient rooms.

- Mounting: Flush-mounted nozzle installed in ceiling
- Connection: Using ADP-AS hose to RDS unit
- Benefits: Safe for electronics, reduces staff exposure, and ensures consistent disinfectant coverage



## ADP-PT

Allows for hand-free decontamination and disinfection of the patient compartment of a fire rescue or ambulance.

- Mounting: Installed inside exterior compartment
- Connection: Using ADP connector on RDS 6110
- Hose length: 8 ft



## APA

used for manual hand- application or remote-head fogging.

- Connection: Using ADP connector on RDS 6110
- Hose length: 25 ft
- Tripod: Optional



## Barcode Capabilities

Rooms and assets may be tagged with standard barcodes for easy retrieval of configuration data by the onboard asset tracking software.

