

Vehicle Decontamination

ADP-CC



Designed to protect your crew

How often is a fire engine the first vehicle at an accident scene? How frequently is a non-transport BLS/ALS paramedic the first to provide emergency treatment to a patient?

The ADP-CC is designed to decontaminate the crew cab using AeroClave's hands-free disinfectant system.



Benefits

- Reduces your staff's exposure to dangerous pathogens
- Fast turnaround and hands-free technology allows you to redeploy staff to highest and best use
- Consistent and reliable delivery of disinfectant, not achievable through manual cleaning methods
- Extremely easy to use with minimal training required
- Fully utilize the capabilities of your RDS unit
- Safe for sensitive electronic equipment
- Low cost of operation; approximately \$1/run

Components

The ADP-CC is installed on the outside of the vehicle and a nozzle assembly is mounted in the interior patient compartment. These are linked with two lengths of color coded tubing that is easily fed through the structure of the vehicle.

ADP-CC SPECIFICATIONS

- Maximum treatment area: 700 cubic ft
- RDS compatibility: RDS 3110 and RDS 6110
- Kit includes:

- ADP Panel Mount



- Dimensions: (Dia) 3.0in x (D) 2.5in
- Material: Polypropylene
- Connection: AeroClave's ADP plug-and play

- Exterior Cover



- Dimensions: (L) 4.75in x (W) 3.75in x (D) 1.25in
- Type: Weather-Resistant
- Material: Thermoplastic Glass-Filled

- Nozzle assembly



- Dimensions: (L) 1.5in x (W) 1.5in x (D) 2.25in
- Material: Stainless steel and plastic

- Tubing: Two 10 ft 1/4 inch polyurethane lengths

- Warranty: 12 month parts and labor
- Training: Available online or on-site

Please call us at
800.788.9119

Overview

The ADP-CC is designed to utilize your RDS unit to fog the crew compartment of fire engines, ladder trucks and other vehicles. AeroClave's automated process ensures consistent operation and results, disinfecting even those hard-to-reach surfaces.



How does it work?

Connect one end of the ADP-AS hose to the RDS and the other to the ADP-CC on the vehicle. Open all interior cabinets and close the exterior doors. Set the RDS to AMBULANCE or PORT MODE and push the start button. The process virtually eliminates the human element of disinfecting, allowing for consistent results. Best of all, it's all done in less than 20 minutes.

ADP-CC CONNECTION




Compatible with RDS systems

Every AeroClave RDS unit has at least one ADP port as standard equipment. Optional models are equipped with up to three (3) ADPs for even more flexibility.

Installation

Easily installed in under 30 minutes. The kit comes with everything you need to install as an OEM, after-market or DIY installer.



Required Hose

This solution requires the use of one of our dual-headed hoses.

Part Number: ADP-AS



AeroClave, LLC
4007 Forsyth Road
Winter Park, FL 32792
Phone: 800.788.9119
Web: www.aeroclave.com

Decontamination Technology